

PBX4L-4C-120200-S (article no.: 83600)

TECHNICAL SPECIFICATION		
<i>Load</i>	Max. Patient weight, [kg]	200
	Safe Working, [kg]	250
	Lifting Pole, [kg]	80
<i>Dimensions</i>	External of the Bed (W x L), [cm]	approx. 132 x 207
	Mattress support platform (W x L), [cm]	120 x 200
	Under bed clearance, [cm]	approx. 16
<i>Adjustment</i>	Height, [cm]	approx. 40 ÷ 80
	Back Rest section, [°]	approx. 0 ÷ 70
	Upper Leg Rest section, [°]	approx. 0 ÷ 35
	Lower Leg Rest section, [°]	approx. 0 ÷ 20
<i>Mattress</i>	Dimensions (W x L), [cm]	120 x 200
	Maximum thickness, [cm]	12
	Volume density of foamed material, [kg/m ³]	35 - 50
<i>Drive system</i>	Control Box	LINAK CB6S
	Lifting Hi-Lo Actuator	LINAK LA34
	Back Rest / Leg Rest Actuator	LINAK LA27
	Handset	LINAK HL74 Strengthened
	Input voltage	230V AC, 50/60Hz
	Output voltage	24V DC
	Power input	Max. 2A
	Operating time	10%, 2 min ON / 18 min OFF
	Ingress protection	IP X6 (Control Box) / IP X4 (Actuators, Handset)
	Electrical appliance class	II
	Noise level	< 65 dB (A)
<i>Weight</i>	Total, [kg]	150,6
	Mattress Support Platform (Head End Section / Leg End Section), [kg]	29,0 / 28,0
	Scissor Lift with Hi-Lo Actuator, [kg]	50,0
	Back Rest / Leg Rest Actuator, [kg]	1,5 / 1,5
	Handset / Control Box, [kg]	0,3 / 1,8
	End Board (1), [kg]	11
	Full-length Side Rail (1 lath), [kg]	2,8
	Lifting Pole with Triangle Handle, [kg]	5,3
<i>Operating conditions</i>	Temperature, [°C]	+10 ÷ +40
	Humidity, [%]	30 ÷ 75
<i>Storage / Transport conditions</i>	Temperature, [°C]	-20 ÷ +50
	Humidity, [%]	30 ÷ 75

**ATTENTION!**

Measurement tolerance: ±10 mm / ±0,5 kg / ±1,5°.

The technical data are valid in optimal ambient conditions for a Bed in standard configuration, which has never been modified or damaged.